

Modificationcard for: EG 750 f. 4press
Part No. : 316800
Print Date: 08-11-02

DATE	Lev.	+	Tekst (DK).	Description
23/11-99	1		1 maskine til Scitex Israel En ramme konstruktion Racks m. 17/8" valser som R2 Speed Analog elektronik, Alu valser i dry. Blæsekanaler med radialblæser og trådvarmelegemer	1series Single frame construction Racks with 1 7/8" rollers Analog electronics, ALU rollers in dryer Radial blowers and wire heater in dryer
23/11-99	2		PU rollers in dry	PU rollers in dry
6/12-99	3	+	Udgangsvalse dev fix wash 1" blød gummi øverst og nederst	1" rubber rollers in outlet dev., fix. and wash
3/5-00	4		Alu valser i dry	Alu rollers in dryer rack
8/5-00	5		Hver anden guide i bund af rack erstattet med gråt mellemstykke	Half of bottom guides replaced by grey spacer
23/6-00	6	+	Dry rack flyttet 10mm tættere på vandrack. 7105 læber på dividing plate, slids til dry drivaksel gjort bredere (rettet fra ingen læber 9/8-01 CV)	Dry rack moved 10mm closer to the wash rack. 7105 lips on dividing plate, slot for dry driving axle extended.
25/8-00	7	+	Dev rack øverste indgangsvalse ændret fra 1" blød gummi til 17/8" Pu, ingen fjedre , rustfri guide 129612 fjernet for at optimere indføring af opadkrumme film	Dev. rack upper inlet roller changed from 1" soft rubber to 1 7/8" smooth PU, no springs. Stainless guide 129612 removed to optimize input of upward curly films.
15/9-00	8	+	Fix + vand rack nederste udgangsvalse pos. 85-000 ændret til glat PU samt 13/16" blød gummi valse pos. 82-000 monteret for at undgå at opadkrumme film kører ovenud af racks	Fix + wash racks: Lower outlet roller, position 85-000 changed to smooth polyurethane. 13/16" Soft rubber roller position 82-000 fitted. Improves transport of upwards curly film.
21/11-00	9		Dry rack hævet med 5mm med 1 pulley under forreste fixerings skrue tandindgreb i gear train justeres. For at forbedre transport af opad krumme film (tekn info #28)	Dry rack raised 5mm. Gear train mesh adjusted. To improve transport of upwards curly film
17/4-01 5/1-01	10	+	3uF kondensator nr.29005 i serie med udsugningsblæser for at sænke kapacitet og nedsætte fordampning. Fra 5/1-01 Drivaksel dry rack flyttet 24mm mod vandrack, sidebox 316181 modificeret se tekn info # 30	3uF capacitor part no. 29005 in series with exhaust blower to reduce capacity and reduce evaporation from tanks. Since 5/1-01 Driveaxle dry rack moved 24mm towards washrack, sidebox 316181 modified to give room for axle.
16/08-02	11		Dry rack med blåt 78T tandhjul for bedre transport af lange film	Dryer rack with blue 78T gearwheel to optimize transportation of long films