

Modificationcard for: EGP 901 Dolev 800	Part No. : 320811
--	--------------------------

Rev.nr.: 01

Print Date: 15-11-02

DATE	Lev.	+	Tekst (DK).	Description (Eng. Tekst).
25/9-01	1		Første serie som 320831 niveau 6 Rack D 320716, F 320727 med guide 320811 , W 320737 Med guide 305458 og 320821, nederste indvalse 1 7/8" udgangsvalse ekstra tiltet i skrå lejer med 1" rustfri valse øverst. 320747, 320757,320767 Gennemløbskontrol med udgangssensor	First series as 320831 level 6 Rack D 320716, F 320727 with guide 320811, W320737 with guide 305458 and 320821, lower input roller tilted in offset bearings, 1" stainless roller in top 320747,320757, 320767 in plate section Film transport control with outletsensor
4/10-01	2	+	En modstand på 68 Kohm monteres parrallelt over R108 som er på 10 Kohm. Senere bliver R108 ændret til 8,87 Kohm For at undgå at drivmotoren stopper hvis forsynings spændingen er høj (f.eks 237V og trafo står på 208v). tekn. info #34	A resistor 68Kohm connected parrallel to R108 which is 10Kohm. Later R108 is changed to 8.87Kohm. Problem were drive motor stopping occasionally at high supply voltage. (E.g. input 237V. and trafo connected for 208V)
24/10-01	3	+	Kabelsæt til dry relæer 305349 skal monteres ekstra flex 809110 ved spadsko. Trafo, to hvide ledninger forsynes med flex 809101. Hullerne i motorkassen til ekstra motor aksler lukkes med gummitulle 9160	Cableset for dryer relays 305349 fitted with extra flex 890110 at spade connectors. Trafo, the 2 white wires fitted with flex 809101. Holes in motor box for extra motoraxles closed with grommet 9160
23/11-01	4	+	Vægt valser fjernet fra act og stab rack. Tandhjul på øverste udgangs valser i act, stab, wash2 fjernet.	Load rollers on output rollers of act and stab rack removed. Gearwheels on top output rollers act, stab, wash2 removed
12/08-02	5	+	Nyt CPU PCB MK4 305216 med feedback på conv. motor styring	New CPU PCB MK4 305216 improved conveyor motor control with feedback
1/5-02	6		3-Fase relæ print 305219/305296, erstattet med 1-fase relæ print 305297 + 13 konnektere for tørrer sektioner. 8489 + 8490 Interconnection diagram 6361 + 6359	3-Phase relay PCB. 305219/305296 replaced with 1-phase relay PCB 305297 + 13 connector for dryer sections. 8489 + 8490 Interconnection diagram 6361 + 6359
12/08-02	7		Ny 3 fase main sw box 305548	New 3 phase main sw. box 305548
5/01-02	8		Drain system med silicone slanger uden spændebånd	Drain system with silicone hoses, no hose clamps fitted

