



Rackside, left.

Bold=high



Rackside, Left
316352



Handle for rackside
10-010
2 pcs

Guide Top
25-000
1 pcs
DEV & WASH

Roller 17/8" PU
In Dev + Wash
50-000
1 pcs

Blade Guide
25-000
1 pcs
ONLY IN FIX

Screw
10-015
4 pcs
+
Flatwasher
10-020
4 pcs
+
Nut
10-017
4 pcs

Roller
81-000
1 pcs

Roller PU In Fix + Wash
Roller SR In Dev
85-000
1 pcs

Roller 13/16" SR
82-000
1 pcs

Roller PU
60-000
3 pcs

Guide Bar
32-005
1 pcs

Roller SR
78-000
1 pcs

Roller PU
76-000
1 pcs

Optional Z-guide
30-000
1 pcs

Crossover Guide
32-000
58 pcs

OUT

IN

Liquid level fix
Liquid level water

Alternative fix level
for emulsion up

Liquid level dev

Roller SR In Dev + Wash
Roller PU In Fix
55-000
1 pcs


Outlet Guide
35-000
1 pcs
+
Screw
88021
4 pcs
+
Springwasher
88201
4 pcs

Spacer
129024
4 pcs
+
Screw
88100
8 pcs
+
Springwasher
88202
8 pcs

Rackside, right.

Guide Fork
913844
4 pcs

Screw
88023
4 pcs



Rackside, Right
316362

L	65271	16T Ø 1/4"	1 pcs
M	65270	16T D 1/4"	5 pcs
G1	276154	24T Ø 10,2	1 pcs
G8	217164	24T Ø 10,2	3 pcs
P	65266	30T 1/4" In - D	8 pcs
X	117528	32T NV 16	1 pcs
SH	117518	36T NV 16	1 pcs
S	65502	36T Ø 10mm MSH	1 pcs
U	65139	80T Ø 10mm MSH	1 pcs

A- K&E 9383- Valsler tydeliggjort i D/F/W rack, tandhjul rettet 11.01.02 CV

This Document contains proprietary data of Echo Graphic.
No information, reproduction or use of any part thereof may be used without written permission.

Tolerance unless otherwise specified: machined surfaces D3 2768-1
measurements under 120mm after folding ±0.5

More Than	Incl.	Tol.	Surface Treatment
(0,5)	±	0,1	
(6)	±	0,2	
(30)	±	0,3	
(120)	±	0,5	
(315)	±	1,000	
(1000)	±	1,5	

Material:

Handwerkervej 2-6
DK-9660 Hadsund Denmark

Designer: JLJ
Name: D/F/W rack 75cm R2 w. guide

Drawn: JLJ
Date: 05.07.01
Scale: 1:1,5

Material: Kar:
Drawing no.: 316487
A

Telefon 98571955
Telefax 98571591